

Type R4 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R4-300B03](#)



Type R4 1.7 Ohms Braking Resistor For 460 V 300 H P 150%
Braking Torque 30% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	150 %
Catalog Number	R4-300B03
Duty Cycling	30 %
Enclosure Type	(2)ED5
Horsepower - Maximum	300
Resistance Ohms	1.7 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Product Assets

[Specifications - R4-300B03](#)