

R4-7.5A02 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-7.5A02](#)

460 V 7.5 H P 100% Braking Torque 20% Duty 100 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE4
Horsepower - Maximum	7.5
Nominal Current (A)	5592.75
Resistance Ohms	100 Ohm
System Voltage	460 V

Dimensions

Depth	5 in
Length	12.375 in
Width	13 in