

# R4-50A02 | Powerohm Braking Resistor

By Powerohm Resistors  
Catalog # [R4-50A02](#)

460 V 50 H P 100% Braking Torque 20% Duty 15 Ohms



## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	20 %
Enclosure Type	GCE18
Horsepower - Maximum	50
Resistance Ohms	15 Ohm
System Voltage	460 V

## Dimensions

Depth	10 in
Length	26.375 in
Width	10 in

## Product Assets