

Type R4 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R4-15A02](#)



Type R4 50 OhmsBraking Resistor For 460 V 15 H P 100%
Braking Torque 20% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	100 %
Catalog Number	R4-15A02
Duty Cycling	20 %
Enclosure Style	NEMA 1

Enclosure Type	GCE8
Horsepower - Maximum	15
Nominal Current (A)	11185.5
Resistance Ohms	50 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	19.375 in
Width	13 in

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R415A02](#)