

# Type R4 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R4-300B02](#)



Type R4 1.7 Ohms Braking Resistor For 460 V 300 H P 150%  
Braking Torque 20% Duty Variable Frequency Drives

## Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

## Application

Powerohm

## General

Braking Torque	150 %
Catalog Number	R4-300B02
Duty Cycling	20 %
Enclosure Type	ED6
Horsepower - Maximum	300
Resistance Ohms	1.7 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Product Assets

[Specifications - R4-300B02](#)