

Type R4 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R4-5B10](#)



Type R4 100 OhmsBraking Resistor For 460 V 5 H P 150%
Braking Torque 100% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	150 %
Catalog Number	R4-5B10
Duty Cycling	100 %
Enclosure Type	GCE15
Horsepower - Maximum	5
Resistance Ohms	100 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R45B10](#)