

# Type R5 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R5-150A05](#)



Type R5 7.8 Ohms Braking Resistor For 575 V 150 H P 100%  
Braking Torque 50% Duty Variable Frequency Drives

## Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

## Application

Powerohm

## General

Braking Torque	100 %
Catalog Number	R5-150A05
Duty Cycling	50 %
Enclosure Type	ED6
Horsepower - Maximum	150
Resistance Ohms	7.8 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

## Product Assets

[Specifications - R5-150A05](#)