

Type R5 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R5-5B01](#)



Type R5 160 OhmsBraking Resistor For 575 V 5 H P 150%
Braking Torque 10% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	150 %
Catalog Number	R5-5B01
Duty Cycling	10 %
Enclosure Type	GCE2
Horsepower - Maximum	5
Resistance Ohms	160 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

Product Assets

[Specifications - R5-5B01](#)