

Type R5 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R5-15A02](#)



Type R5 78 OhmsBraking Resistor For 575 V 15 H P 100%
Braking Torque 20% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R5-15A02
Duty Cycling	20 %
Enclosure Type	GCE8
Horsepower - Maximum	15
Resistance Ohms	78 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R515A02](#)