

Type R5 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R5-7.5B10](#)



Type R5 100 OhmsBraking Resistor For 575 V 7.5 H P 150%
Braking Torque 100% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	150 %
Catalog Number	R5-7.5B10
Duty Cycling	100 %
Enclosure Type	GCE24
Horsepower - Maximum	7.5
Resistance Ohms	100 Ohm
System Voltage	575 V
Type	R5 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R575B10](#)