



Box, FRP, 10"x15"x12", Tier 8, Mouseholes

By QUAZITE
Catalog # B10101512M

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
QuaziteFRP	Yes
Type	Below Ground Boxes
UPC	662037175610

Dimensions

Dimensions	15 in x 10 in x 12 in
Height	12 in
Length	15 in
Weight	23.1 lb
Width	10 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)