



Box, FRP, 30"x48"x48", Tier 8

By QUAZITE
Catalog # B1A304848B

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
QuaziteFRP	Yes
Type	Below Ground Boxes
UPC	662037159092
Weight Load Rating (Design/Test)	8,000/12,000 lb

Dimensions

Dimensions	48 in x 30 in x 48 in
Height	48 in
Length	48 in
Weight	252 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 30 X 48 X 48 Box Integral Bottom Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)