



Cover, FRP, Tier 15, 24"x24"

By QUAZITE

Catalog # [C12242402A009](#)

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Catalog Number	C12242402A009
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	24 in x 24 in x 2 in
Height	2 in
Length	24 in
Weight	105 lb
Width	24 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite 24 X 24 X 2 Cover Standard Version](#)

[Video - Hubbell Power Systems How to Install Small Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)

[Video - Hubbell Power Systems PG3660 Retrofit Kit](#)



A Hubbell brand