



Box, FRP, 30"x48"x36", Tier 15, Solid Bottom

By QUAZITE
Catalog # B1B304836B

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|-------------------------|--------------------|
| Catalog Number | B1B304836B |
| EU RoHS Indicator | No |
| Insulated? | No |
| Load Rating (ANSI Tier) | T15 |
| Material | Fiberglass |
| QuaziteFRP | Yes |
| Type | Below Ground Boxes |
| UPC | 662037159276 |



*Representative Image

Weight Load Rating (Design/Test) 15,000/22,000 lb

Dimensions

| | |
|------------|-----------------------|
| Dimensions | 48 in x 30 in x 36 in |
| Height | 36 in |
| Length | 48 in |
| Weight | 234 lb |
| Width | 30 in |

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 30 X 48 X 36 Box W/ Integral Bottom](#)
- [Specifications - B1B304836B](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)