



Extension, FRP, 13"x24"x8", Tier 8

By QUAZITE
Catalog # [E00132408A](#)

Quazite ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	662037157050

Dimensions

Dimensions	24 in x 13 in x 8 in
Height	8 in
Length	24 in
Weight	34.65 lb
Width	13 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Sales Drawings - Quazite 13 X 24 X 08 Extension Standard Version \(E00132408A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.