



## Cover, FRP, Tier 15, 11"x32"

By QUAZITE

Catalog # [C02113202A009](#)

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
UPC	662037180874
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	32 in x 11 in x 2 in
Height	2 in
Length	32 in
Weight	45.15 lb
Width	11 in

### Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite 11 X 32 X 02 Cover Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand