



Extension, FRP, 48"x72"x12", Tier 8, Solid Bottom

By QUAZITE
Catalog # EOA487212B

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	066203716354

Dimensions

Dimensions	72 in x 48 in x 12 in
Height	12 in
Length	72 in
Weight	276 lb
Width	48 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 48 X 72 X 12 Extension Integral Bottom Standard Version](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)