



Cover, FRP, Tier 15, 15"x17"

By QUAZITE
Catalog # [C02151702A050](#)



Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Fiberglass Reinforced Polymer
UPC	066203718723
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	17 in x 15 in x 2 in
Height	2 in
Length	17 in
Weight	26.25 lb
Width	15 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 15 X 17 X 02 Cover Standard Version](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)
- [Video - Hubbell Power Systems PG3660 Retrofit Kit](#)