



Extension, FRP, 48"x78"x36", Tier 8

By QUAZITE
Catalog # [EOA487836A](#)

Quazite® ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|-------------------------|-------------------------------|
| Insulated? | No |
| Load Rating (ANSI Tier) | T8 |
| Material | Fiberglass-Reinforced Polymer |
| QuaziteFRP | Yes |
| Type | Below Ground Box Extensions |
| UPC | 662037164355 |

Dimensions

| | |
|------------|-----------------------|
| Dimensions | 78 in x 48 in x 36 in |
| Height | 36 in |
| Length | 78 in |
| Weight | 331 lb |
| Width | 48 in |

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 48 X 78 X 36 Extension Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)