



## Extension, FRP, 36"x60"x12", Tier 15, Solid Bottom

By QUAZITE  
Catalog # EOB366012B



\*Representative Image

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	066203716122

### Dimensions

Dimensions	60 in x 36 in x 12 in
Height	12 in
Length	60 in
Weight	209 lb
Width	36 in

### Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 36 X 60 X 12 Extension W/ Integral Bottom Standard Version](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)