



Extension, FRP, 48"x48"x12", Tier 15

By QUAZITE
Catalog # EOB484812A

Quazite® ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass-Reinforced Polymer
QuaziteFRP	Yes
Type	Below Ground Box Extensions
UPC	662037162962

Dimensions

Dimensions	48 in x 48 in x 12 in
Height	12 in
Length	48 in
Weight	252 lb
Width	48 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 48 X 48 X 12 Extension Bottom Extension Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)