



Extension, FRP, 30"x60"x12", Tier 15

By QUAZITE
Catalog # EOB306012A

Quazite® ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Catalog Number	EOB306012A
Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass
QuaziteFRP	Yes
Type	Below Ground Box Extensions
UPC	662037160395



*Representative Image

Dimensions

Dimensions	60 in x 30 in x 12 in
Height	12 in
Length	60 in
Weight	139 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 30 X 60 X 12 Extension Standard Version](#)
- [Specifications - EOB306012A](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)