



Cover, Polymer Concrete, Tier 15, 17"x30"

By QUAZITE
Catalog # PG1730HA0010

Quazite® ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037109912
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	30 in x 17 in x 2 in
Height	2 in
Length	30 in
Weight	82 lb
Width	17 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 17 X 30 Cover Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand