



Extension, FRP, 30"x60"x12", Tier 15, Solid Bottom

By QUAZITE
Catalog # [EOB306012B](#)



*Representative Image

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|-------------------------|-----------------------------|
| Catalog Number | EOB306012B |
| Insulated? | No |
| Load Rating (ANSI Tier) | T15 |
| Material | Fiberglass |
| Type | Below Ground Box Extensions |
| UPC | 066203716040 |

Dimensions

| | |
|------------|-----------------------|
| Dimensions | 60 in x 30 in x 12 in |
| Height | 12 in |
| Length | 60 in |
| Weight | 159 lb |
| Width | 30 in |

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite 30 X 60 X 12 Extension W/ Integral Bottom Standard Version](#)
- [Specifications - EOB306012B](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)