



Cover, Polymer Concrete, Tier 22, 17"x30"

By QUAZITE
Catalog # [PG1730HH0017](#)

Quazite® ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

Catalog Number	PG1730HH0017
EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete



*Representative Image

UPC	662037144012
Weight Load Rating	22,500/33,750 lb

Dimensions

Dimensions	30 in x 17 in x 2 in
Height	2 in
Length	30 in
Weight	85 lb
Width	17 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite Cover](#)
- [Specifications - PG1730HH0017](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)