



Extension, FRP, 36"x60"x12", Tier 22

By QUAZITE
Catalog # [EOC366012A](#)

Quazite ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T22
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions

Dimensions

Dimensions	60 in x 36 in x 12 in
Height	12 in
Length	60 in
Weight	182 lb
Width	36 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-EOC366012A-SPEC-EN | REV 1/2024