



Cover, Polymer Concrete, Tier 15, 12"x12"

By QUAZITE
Catalog # [PC1212HA0046](#)

Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037107635
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	12 in x 12 in x 1 in
Height	1 in
Length	12 in
Weight	10 lb
Width	12 in

Product Assets

[Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - PC1212HA00](#)

[Video - PenCell® How It's Made \(VI07068E0617\)](#)

[Video - PenCell® Enclosures \(VI07062E0617\)](#)

[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-PC1212HA0046-SPEC-EN | REV 1/2024