



2-1/2 in. Rigid/IMC Sealing Locknut

By Raco
Catalog # 1207

2-1/2 in. Rigid/IMC Sealing Locknut



*Representative Image

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Economical alternative to a threaded enclosure connector
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 4 in.

General

| | |
|--------------------------|----------------------|
| Conduit Type | Rigid/IMC |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Wet Location |
| Fitting Type | Locknuts |
| Material | Steel |
| UPC | 050169012079 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 0.169 in x 3.535 in x 3.535 in |
| Height | 3.535 in |
| Length | 0.169 in |
| Trade Size | 2-1/2 in |
| Weight | 0.124 lb |
| Width | 3.535 in |

Certifications And Compliance

| | |
|----------------------|---|
| Certified Listed | <ul style="list-style-type: none">• UL Listed• CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 30 |
| Minimum Pack Quantity | 30 |
| Pallet Quantity | 6720 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969-1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1207-SPEC-EN | REV 6/2024