



## 2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

By Raco  
Catalog # 1228

2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated



\*Representative Image

### Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #1/0 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

### General

Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012284

### Dimensions

Dimensions	1.953 in x 2.719 in x 3.219 in
Height	3.219 in
Length	1.953 in
Trade Size	2 in
Weight	0.372 lb
Width	2.719 in

### Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	6300

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-1228-SPEC-EN | REV 6/2024