



Cover, Polymer Concrete, Tier 15, 24"x24"

By QUAZITE
Catalog # [PG2424HA0017](#)

Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Polymer Concrete
UPC	662037131593
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	24 in x 24 in x 2 in
Height	2 in
Length	24 in
Weight	100 lb
Width	24 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite Cover \(PG2424HA00\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-PG2424HA0017-SPEC-EN | REV 1/2024