



## Floor Mount Connectors - Uninsulated

By Raco  
Catalog # 1808



2 in. Rigid/IMC Compression Connector, Uninsulated

### Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 4 in.

### General

Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Yes
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169018088

### Dimensions

Dimensions	2.219 in x 2.75 in x 2.75 in
Height	2.75 in
Length	2.219 in
Trade Size	2 in
Weight	0.803 lb
Width	2.75 in

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1225

### Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195969- 1](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 1808](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-1808-SPEC-EN | REV 6/2024