



Cover, Polymer Concrete, Tier 22, 30"x48"

By QUAZITE
Catalog # [PG3048HH0009](#)



Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.

*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Polymer Concrete
UPC	662037130565
Weight Load Rating (Design/Test)	22,500/33,750 lb

Dimensions

Dimensions	48 in x 30 in x 3 in
Height	3 in
Length	48 in
Weight	217 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite Heavy Duty Cover \(PG3048HH00\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-PG3048HH0009-SPEC-EN | REV 1/2024