



1 in. Rigid/IMC Locknut

By Raco
Catalog # 1004

1 in. Rigid/IMC Locknut



*Representative Image

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- For use in dry locations
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 6 in.

Application

For use in dry locations on threaded rigid/IMC conduit to secure conduit to a box or enclosure

General

| | |
|--------------|--------------|
| Conduit Type | Rigid/IMC |
| Fitting Type | Locknuts |
| Material | Steel |
| UPC | 050169010044 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 0.203 in x 1.766 in x 1.766 in |
| Height | 1.766 in |
| Length | 0.203 in |
| Trade Size | 1 in |
| Weight | 0.037 lb |
| Width | 1.766 in |

Certifications And Compliance

| | |
|----------------------|---|
| Certified Listed | <ul style="list-style-type: none">• UL Listed• CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 100 |
| Pallet Quantity | 44100 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969-1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1004-SPEC-EN | REV 6/2024