



2 in. EMT Raintight Compression Connector, Insulated

By Raco
Catalog # 2918RT



2 in. EMT Raintight Compression Connector, Insulated

*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insulated
- Marked with "Wet Location" for easy inspection
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

General

| | |
|--------------------------|----------------------|
| Conduit Type | EMT |
| Connector Type | Compression |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Wet Location |
| Fitting Type | Connectors |
| Insulation Type | Insulated |
| Material | Steel |
| UPC | 050169291894 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 2.467 in x 2.607 in x 2.78 in |
| Height | 2.78 in |
| Length | 2.467 in |
| Trade Size | 2 in |
| Weight | 0.578 lb |
| Width | 2.607 in |

Certifications And Compliance

| | |
|----------------------|--------------|
| Certified Listed | cULus Listed |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 10 |
| Pallet Quantity | 2080 |

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[Sales Drawings - 2912RT](#)
[SDS - HCC_SDS](#)
[Sell Sheets - Raintight Steel EMT Compression Fittings](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2918RT-SPEC-EN | REV 6/2024