



4 in. Rigid/IMC Locknut

By Raco
Catalog # 1016

4 in. Rigid/IMC Locknut



*Representative Image

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- For use in dry locations
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 6 in.

Application

For use in dry locations on threaded rigid/IMC conduit to secure conduit to a box or enclosure

General

Conduit Type	Rigid/IMC
Fitting Type	Locknuts
Material	Steel
UPC	050169010167

Dimensions

Dimensions	0.17 in x 5.29 in x 5.29 in
Height	5.29 in
Length	0.17 in
Trade Size	4 in
Weight	0.213 lb
Width	5.29 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	6860

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969-1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1016-SPEC-EN | REV 6/2024