



## 3/8 in. 90 Degree Liquidtight Connector, Insulated

By Raco  
Catalog # 3541RAC



3/8 in. 90 Degree Liquidtight Connector, Insulated

\*Representative Image

### Features

- Patented split gland-ring is designed to slip onto the conduit quickly and to grip the jacket of the conduit, speeding installation, assuring a perfect seal and preventing pullouts
- RACO liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
- All steel/iron components are zinc electroplated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- 3/8 in. to 1 in. Steel, 1-1/4 in. to 4 in. Malleable Iron bodies and nuts
- Additional sizes available

### General

Catalog Number	3541RAC
Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Insulated
Material	3541RAC
UPC	050169035412

### Dimensions

Dimensions	1.188 in x 1.188 in x 2.813 in
Height	2.813 in
Length	1.188 in
Trade Size	3/8 in
Weight	0.244 lb
Width	1.188 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Hazardous Rating(s)	Class I, Division 2
	Class II Division 1 & 2
	Class III, Division 1 & 2
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	8000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3541RAC Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-3541RAC-SPEC-EN | REV 6/2024