



5 in. Rigid/IMC Locknut

By Raco
Catalog # 1020

5 in. Rigid/IMC Locknut



*Representative Image

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- For use in dry locations
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 6 in.

General

Application	For use in dry locations on threaded rigid/IMC conduit to secure conduit to a box or enclosure
Catalog Number	1020
Conduit Type	Rigid/IMC
Fitting Type	Locknuts
Material	1020
UPC	050169010204

Dimensions

Dimensions	0.314 in x 6.6 in x 6.6 in
Height	6.6 in
Length	0.314 in
Trade Size	5 in
Weight	0.635 lb
Width	6.6 in

Certifications And Compliance

Certified Listed	UL Listed CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	8
Minimum Pack Quantity	8
Pallet Quantity	1680

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969-1](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1020-SPEC-EN | REV 6/2024