### Catalog # 807C

# 4 IN. SQUARE EXPOSED WORK COVER

## 2-1.406 IN. DIA. RECEPTACLE

Ideal for exposed work environments to support a variety of electrical devices. Our exposed work covers are made from heavy duty, 16-gauge, galvanized steel and come in 22 configurations to fit your needs.

#### FEATURES

- Exposed work covers include break-off lock nuts or required hardware
- Exposed work covers meet the requirements of the 2020 NEC Article 250.146 (A). No bonding jumper is required for covers with: (1) Crushed corners (2) Two or more device attachment fasteners that are permanent with thread-locking, screws, or nut-locking means (3) Insulating retaining washer removed for at least one device attachment screw
- Cover is packed with printed catalog number, compliances and QR code for installation instructions

#### APPLICATIONS

Surface covers are used to support switches or receptacles in areas where the box is surface mounted or positioned in exposed work applications.

#### CERTIFICATIONS



#### SPECIFICATIONS

UPC NUMBER:	050169999820
PRODUCT LENGTH/DEPTH (IN.):	0.56
PRODUCT WIDTH (IN.):	4.12
PRODUCT HEIGHT (IN.):	4.12
WT. PRODUCT. (LBS.):	0.422
PACKAGE TYPE:	LOOSE
PRODUCT UPC-A LABELED:	YES

#### PACKAGING

I2OF5:	50050169999825
STANDARD CARTON QTY	: 10
MIN ORDER QTY:	10





