



2-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

By Raco
Catalog # 1230



*Representative Image

2-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #1/0 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

| | |
|-------------------|----------------------|
| Conduit Type | Rigid/IMC |
| Connector Type | Grounding |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Bushings |
| Insulation Type | Insulated |
| Material | Malleable Iron |
| UPC | 050169012307 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 2.297 in x 3.281 in x 3.906 in |
| Height | 3.906 in |
| Length | 2.297 in |
| Trade Size | 2-1/2 in |
| Weight | 0.429 lb |
| Width | 3.281 in |

Electrical Ratings

| | |
|---------------------------------|----------|
| Grounding Wire Capacity Maximum | #1/0 STR |
| Grounding Wire Capacity Minimum | #14 SOL |

Certifications And Compliance

| | |
|----------------------|----------------------------|
| Certified Listed | UL Listed CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 10 |
| Pallet Quantity | 4950 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1230-SPEC-EN | REV 6/2024