



# 1/2 in. Flex/AC 90 Degree Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco  
Catalog # [2202](#)



\*Representative Image

1/2 in. Flex/AC 90 Degree Squeeze Connector, Uninsulated, for FMC/AC/MC Cable.

## Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

## General

Conduit Type	<ul style="list-style-type: none"><li>• Flexible Metal Conduit</li><li>• Armored Cable/Metal Clad (AC/MC)</li></ul>
Connector Type	Squeeze
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022023

## Dimensions

Dimensions	2.234 in x 1.797 in x 1.54 in
Height	1.54 in
Length	2.234 in
Trade Size	1/2 in
Weight	0.199 lb
Width	1.797 in

## Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

## Logistics

Carton Quantity	100
Pallet Quantity	3000

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - MC\\_BX\\_CONDUIT LOGO](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2202-SPEC-EN | REV 6/2024