



3 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco
Catalog # 2212

3 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable.

Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

General

Catalog Number	2212
Conduit Type	<ul style="list-style-type: none">• Flexible Metal Conduit• Armored Cable/Metal Clad (AC/MC)
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022122

Dimensions

Dimensions	8.969 in x 5.063 in x 6.54 in
Height	6.54 in



*Representative Image

Length	8.969 in
Trade Size	3 in
Weight	5.525 lb
Width	5.063 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	1
Pallet Quantity	224

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - MC_BX_CONDUIT LOGO](#)
- [SDS - HCC SDS](#)
- [Specifications - 2212](#)
- [Terms and Conditions - HCC Terms & Conditions](#)