

HUBBELL Power Systems

Standoff Insulator - 15kV

By Reuel
Catalog # [U-SOI2260BB](#)

15kV Standoff Insulator - High Creep for Indoor and Outdoor
Applications - Overall Length = 6.00 in, Shed Outside Diameter =
3.62 in - (2) 3/8 in-16 Threaded Inserts in each End



General

Application	Stand-Off Insulator - High Creep
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Routine	600 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	2
Number of Bolt Holes - Top Terminal	2
Number of Sheds	7
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	2000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	2.25 in
Diameter - Bottom Terminal Bolt Circle	1.12 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Diameter - Large Shed	3.62 in
Diameter - Top Terminal Bolt Circle	1.12 in
Diameter - Top Terminal Bolt Holes	3/8-16
Diameter - Top Terminal Outside	2.25 in
Length	6 in
Weight	2.4 lb

Electrical Ratings

Minimum Creepage	13.85 in
Minimum Strike	6 in
kV Class	15 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

[Literature - Insulators - Reuel](#)
[Sales Drawings - Stand-Off Insulators \(High Creep\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
REU-USO12260BB-SPEC-EN | REV 6/2024