



3-1/2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco
Catalog # [2214](#)



*Representative Image

3-1/2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

General

Catalog Number	2214
Conduit Type	<ul style="list-style-type: none">• Flexible Metal Conduit• Armored Cable/Metal Clad (AC/MC)
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022146

Dimensions

Dimensions	11.234 in x 6.797 in x 7.5 in
Height	7.5 in
Length	11.234 in
Trade Size	3-1/2 in
Weight	12.155 lb
Width	6.797 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	1
Pallet Quantity	84

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - MC_BX_CONDUIT LOGO](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2214-SPEC-EN | REV 6/2024