



4 in. Square Box, Welded with STAB-IT® Connector, 2-1/8 in. Deep, 600V, Raised Ground, 8 in. #12 Solid Copper Pigtail

By Raco
Catalog # 232S



4 in. Square Box, Welded with STAB-IT® Connector, 2-1/8 in. Deep, 600V, Raised Ground, 8 in. #12 Solid Copper Pigtail

Features

- Welded steel construction
- 4 in. square x 2-1/8 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls
- Includes 8 in. #12 solid copper ground pigtail

Application

- RACO® STAB-IT boxes are great for any job where flexible armored cable is being used
- RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles

General

Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in. Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169500705

Dimensions

Actual Depth	2.2 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.14 in
Raised Ground	Yes
Weight	0.974 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Pallet Quantity	1750

Product Assets

[3D Models - 232S-3D](#)
[Brochures - STAB-IT® Electrical Boxes](#)
[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-5](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Product Logo - STAB-IT](#)
[Sales Drawings - 232S](#)
[SDS - HCC_SDS](#)
[Sell Sheets - RACO® STAB-IT](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: STAB-IT® with Cable Management](#)
[Video - RACO: STAB-IT® vs competition](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-232S-SPEC-EN | REV 6/2024