

# HUBBELL Power Systems

## Standoff Insulator - 25kV

By Reuel

Catalog # [U-SOI2267AA](#)

25kV Standoff Insulator - High Creep for Indoor and Outdoor Applications - Overall Length = 6.75 in, Shed Outside Diameter = 3.62 in - (1) 3/8 in-16 Threaded Insert in each End



\*Representative Image

### General

Application	Stand-Off Insulator - High Creep
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Routine	600 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	1
Number of Bolt Holes - Top Terminal	1
Number of Sheds	8
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	2000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

### Dimensions

Bottom Terminal Diameter	2.25 in
Diameter - Bottom Terminal Bolt Circle	-
Diameter - Bottom Terminal Bolt Holes	3/8-16
Diameter - Large Shed	3.62 in
Diameter - Top Terminal Bolt Circle	-
Diameter - Top Terminal Bolt Holes	3/8-16
Diameter - Top Terminal Outside	2.25 in
Length	6.75 in
Weight	2.7 lb

### Electrical Ratings

Minimum Creepage	15.7 in
Minimum Strike	6.75 in
kV Class	25 kV

### Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

### Product Assets

[Literature - Insulators - Reuel](#)

[Sales Drawings - Stand-Off Insulators \(High Creep\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
REU-USO12267AA-SPEC-EN | REV 6/2024