

HUBBELL Power Systems

Standoff Insulator - 5kV

By Reuel
Catalog # [U-SOI3735CC](#)

5kV Standoff Insulator - Medium Duty for Indoor and Outdoor Applications - Overall Length = 3.50 in, Shed Outside Diameter = 3.75 in - (4) 3/8 in-16 Threaded Inserts in each End; 2.00 in Dia. B.C.



General

Application	Stand-Off Insulator - Medium Duty
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Routine	1500 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	4
Number of Bolt Holes - Top Terminal	4
Number of Sheds	1
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	5000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	3.75 in
Diameter - Bottom Terminal Bolt Circle	2.00 in
Diameter - Bottom Terminal Bolt Holes	3/8-16
Diameter - Large Shed	3.75 in
Diameter - Top Terminal Bolt Circle	2.00 in
Diameter - Top Terminal Bolt Holes	3/8-16
Diameter - Top Terminal Outside	3.75 in
Length	3.5 in
Weight	2.3 lb

Electrical Ratings

Minimum Creepage	4.57 in
Minimum Strike	3.5 in
kV Class	5 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

[Literature - Insulators - Reuel](#)
[Sales Drawings - Stand-Off Insulators \(Medium Duty\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
REU-USOI3735CC-SPEC-EN | REV 6/2024