



4 in. Square Box, Welded, 2-1/8 in. Deep with AC/MC/Flex Clamps, Four Knockouts, BOX-LOC®, MS Bracket, Flush

By Raco
Catalog # 243



4 in. Square Box, Welded, 2-1/8 in. Deep with AC/MC/Flex Clamps, Three 1/2 in. KO's and One TKO, BOX-LOC®, MS Bracket, Flush

Features

- Welded steel construction with "MS" BOX-LOC® bracket which allows for positioning on either side of stud
- 4 in. square x 2-1/8 in. deep
- BOX-LOC® Bracket is a snap to install. Place the bracket on the open side of the stud first. Slots in the bracket engage the lip of the stud
- BX clamps provided for steel and alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- TKO® Knockouts allow for design and installation flexibility
- Supplied with three 1/2 in. and one 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 29.5 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	MS, for Metal Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002438
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Actual Depth	2.188 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.625 in
Raised Ground	No
Weight	1.068 lb
Width	5.5 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1250

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - LEED Statement](#)
- [Certifications - NEMA OS1](#)
- [Sales Drawings - RACO-welded-steel-box-infographic](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Box Positioning Products](#)
- [Sell Sheets - BOX-LOC Metal Stud Bracketed Boxes](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-243-SPEC-EN | REV 6/2024