



Concrete Ring, Welded, 5 in. Deep, Double Row 1/2 & 3/4 in. KO's

By Raco
Catalog # 275

Concrete Ring, Welded, 5 in. Deep, Double Row 1/2 & 3/4 in. KO's



Features

- Flat sides provide excellent contact for locknuts
- External ears are used to nail the ring to the wood form
- Top cover is removable for before-pour work
- Ears on inside of box are for fixtures
- Waxed fixture ears prevent concrete from interfering with the threads
- A variety of covers are available
- Cover plate must be ordered separately with all RACO® concrete rings
- Used in high-rise construction
- 74.0 cu. in. capacity
- Not designed for ceiling fan support, the maximum support load for a static fixture is 50 lbs

General

Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in;3/4 in
Material	Steel
Type	Concrete Ring
UPC	050169002759
Wiring System	Conduit

Dimensions

Cubic Capacity	61.5 cu.in
Depth	5 in
Fixture Lbs.	50 lb
Height	4 in
Weight	1.3 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	10
Packaging Type	No Packaging
Pallet Quantity	550

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-275-SPEC-EN | REV 6/2024