

Station Post Insulator - 25kV / 35kV

By Reuel
Catalog # [U-SPI5210](#)

25kV / 35kV Station Post Insulator - Indoor and Outdoor
Applications - Overall Length = 10.00 in, Top End Outside
Diameter = 5.25 in, Bottom End Outside Diameter = 5.25 in - (4)
1/2 in-13 Threaded Inserts in each End; 3.00 in Dia. B.C.

Features

- Station post insulator
- indoor & outdoor applications

Application

Station Post Insulator

General

Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Max.	2500
Catalog Number	U-SPI5210
Color	Gray
Indoor/Outdoor	Either
Number of Bolt Holes - Bottom Terminal	4
Number of Bolt Holes - Top Terminal	4
Number of Sheds	15
Plating - Bottom Terminal	Unplated
Press Minimum	30000
Tensile Strength	12000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic
UPC	096359823308

Dimensions

Bottom Terminal Diameter	5.25 in
--------------------------	---------



*Representative Image

Diameter - Bottom Terminal Bolt Circle	3.00 in
Diameter - Bottom Terminal Bolt Holes	1/2-13
Diameter - Large Shed	5.25 in
Diameter - Top Terminal Bolt Circle	3.00 in
Diameter - Top Terminal Bolt Holes	1/2-13
Diameter - Top Terminal Outside	4.38 in
Dimensions	5.25 in x 5.25 in x 10.00 in
Height	10 in
Length	5.25 in
Weight	10.84 lb
Width	5.25 in

Electrical Ratings

Minimum Creepage	31.5 in
Minimum Strike	10 in
kV Class	25 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

- [Catalogs - Reuel Insulators](#)
- [Literature - Insulators - Reuel](#)
- [Sales Drawings - Station Post Insulator](#)
- [Specifications - USPI5210](#)