

HUBBELL Power Systems

Station Post Insulator - 15kV

By Reuel
Catalog # [U-SPI6010](#)

15kV Station Post Insulator - Indoor and Outdoor Applications - Overall Length = 10.00 in, Top End Outside Diameter = 4.50 in, Bottom End Outside Diameter = 5.00 in - (4) 1/2 in-13 Threaded Inserts in each End; 3.00 in Dia. B.C.



*Representative Image

General

Application	Station Post Insulator
Bottom Terminal Type	Aluminum Threaded Inserts
Cantilever Bending Strength - Max.	2000
Cantilever Bending Strength - Routine	2000 lb
Color	Gray
Number of Bolt Holes - Bottom Terminal	4
Number of Bolt Holes - Top Terminal	4
Number of Sheds	9
Plating - Bottom Terminal	Unplated
Press Minimum	20000
Tensile Strength	10000 lb.
Top Terminal Plating	Unplated
Top Terminal Type	Aluminum Threaded Inserts
Torsional Strength	-
Type	Cast Epoxy Cycloaliphatic

Dimensions

Bottom Terminal Diameter	5 in
Diameter - Bottom Terminal Bolt Circle	3.00 in
Diameter - Bottom Terminal Bolt Holes	1/2-13
Diameter - Large Shed	5.00 in
Diameter - Top Terminal Bolt Circle	3.00 in
Diameter - Top Terminal Bolt Holes	1/2-13
Diameter - Top Terminal Outside	4.50 in
Length	10 in
Weight	10 lb

Electrical Ratings

Minimum Creepage	20.8 in
Minimum Strike	10 in
kV Class	15 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.9
----------------------	------------

Product Assets

[Literature - Insulators - Reuel](#)
[Sales Drawings - Station Post Insulators](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
REU-USPI6010-SPEC-EN | REV 6/2024